



BRACKETS INDICATE
AQUA SYSTEMS
COMPONENT SUPPLY

PEDI OPERATING INSTRUCTIONS

Portable Exchange Deionization (PEDI) provides high quality water on demand. This is accomplished through the use of high quality DI exchange resins. Exchange resins operate through energy supplied by a pressurized flowing stream of water. Loss of flow will cause the DI water to become stale. Once stale, the quality indicator will show poor water quality. Systems sitting idle with no water flow will indicate poor water quality at time of usage. To correct this issue follow the below steps:

- Flush System to Quality**
1. Open the system to drain at a controlled rate of flow
 2. Rate of flow should not exceed
 - a. 2 gpm for 1.2 Cubic Foot Mixed Bed Units
 - b. 3.5 gpm for 1.2 Cubic Foot Dual Bed Units
 - c. 6 gpm for 3.6 Cubic Foot Mixed Bed Units
 - d. 10 gpm for 3.6 Cubic Foot Dual Bed Units
 3. Allow unit to flow 7 to 10 minutes.
 4. When water quality desired is achieved, stop drain line flush and return system to service.
 5. If after 10 minutes of quality flush the units have not returned to quality stop flush. Units are exhausted and need replaced.
 6. Remove tank (s) from line and exchange for a fresh set.
 7. Call to reorder tanks on an as needed basis.

Additional information may be found on system installation drawing. Also see PEDI Application Guidelines

Should further assistance be needed please call Aqua Systems Commercial/Industrial department at 317-272-6715

*** QUALITY LIGHTS SHOWN FOR ILLUSTRATION ONLY**

ITEM #	QTY	PART #	DESCRIPTION
1	12'	04110710	0.75" Grey Pureflex Water Hose
2	6	08080121	Size 10 Stainless Steel Clamp
3	4	09500104	Union x Male Adaptor 3/4"
4	3	09500103	Union Adaptor x Hose Barb 3/4"
5	3	09500102	Union x Hose Barb 3/4"
6	4	09500101	Male Adaptor 3/4"
7	3	08803146 KKK	3/4" flpt x flpt x flpt Tee
8	1	08803107 K	3/4" Close Nipple PVC
9	1	08803165 K	3/4" Flpt x Flpt Ball Valve
10	1	09500091	2 gpm PVC Flow Control 3/4"
SERVICE IN / OUT KIT			
OPTIONAL COMPONENTS			
14	1	08803165 K	3/4" Flpt x Flpt Ball Valve
15	1	09500101	Male Adaptor 3/4"
16	1	09500104	Union x Male Adaptor 3/4"

AVAILABLE QUALITY LIGHTS

09520120	Resilite 110V 50K ohm 3/4"
09520122	Resilite 110V 1Meg ohm 3/4"
09550102	Pure Light 2 with Trans.
09520121	Resilite 110V 200K ohm 3/4"
09520123	Resilite 110V 2 Meg ohm 3/4"

NOTES:

1. INFORMATION IS SUBJECT TO CHANGE WITHOUT NOTICE.
2. INTERCONNECTING PIPING SHOWN DOTTED IS SUPPLIED BY OTHERS.
3. QUALITY LIGHTS ARE OFFERED SEPARATELY

REV. #	DESCRIPTION	DATE
1	ADDED FLOW CONTROL CHG. OPTIONAL EQUIP.	12/27/2005
2	CHGD UNION X HOSE BARB TO NPT	02/08/2006
3	ADDED NUMBER FUR HOSE & STD VALVE	02/08/2006

DESCRIPTION

0.75" DUAL MIXED BED CONFIGURATION KIT
PAGE 1 OF 1 APPROVED BY: NR DATE: 03/06
PART NUMBER: 15000055

CONFIDENTIAL & PROPRIETARY

This Document including all information contained there on is the exclusive and confidential property of Aqua Systems of Avon, IN. This Document and its information are not to be copied, reproduced or delivered to others in whole or in part without expressed written consent and is loaned subject to return on demand. All rights to design and invention are reserved.

